



Round Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, Bronze

By Bell
Catalog # 5197-2



Round Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, Bronze

Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Three hole covers supplied with two closure plugs
- Installation hardware, gasket, and multilingual instructions included
- Three 1/2 in. outlets
- NEMA 3R rated

General

Color	Bronze
Construction	Metallic
Cover Type	Lampholder/Cluster
Material	Die Cast Aluminum
Number Of Outlets	3
Type	Cover
UPC	050169519721

Dimensions

Actual Depth	1.094 in
Height	4.125 in
Weight	0.406 lb
Width	4.125 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514A
Nema Rating	NEMA 3R

Logistics

Carton Quantity	20
Packaging Type	Shrink
Pallet Quantity	3600
Standard Package	20

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - 5193 series, 5197 series](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BELL-5197-2-SPEC-EN | REV 1/2024