



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



523I 20A 120/277VAC S Wire Comm 3W SW Iv

Pass & Seymour/Legrand

Catalog Number	523I
Manufacturer	Pass & Seymour/Legrand
Description	Commercial 3WAY Switch, Side Wire, 20AMP 120/277VOLT, Ivory.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Three pole
amperage rating	20
connection	Side Wire or external screw-pressure plate
Connection Type	Wired
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
Material	Thermoplastic
media	Yes
Poles	3-way
Switch Type	Toggle
Voltage	120/277 V
Voltage Rating	120/277

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC S WIRE COMM 3W SW I
extra long description	P&S CS20AC3I 20A 120/277VAC S WIRE
Long Description	Commercial 3way Switch, Side Wire, 20amp 120/277volt, Ivory.
Product Type	20A 120/277VAC S Wire Comm 3W SW I
Special Features	Side wire, locking support, heavy duty toggle

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007126532
Manufacturers Part Number	CS20AC3I
UPC	785007126532



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting	WALL
nema rating	WD-1 and WD-6
Operating Temperature	-40°-115°F
standard	CULUS, FEDSPEC, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2