



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9172 E Florentine Road Unit 9  
86314-0000, AZ Prescott Valley  
Phone: 928-356-1174  
Fax: 480-426-8084



## 523I 20A 120/277VAC S Wire Comm 3W SW Iv

*Pass & Seymour/Legrand*

Catalog Number	523I
Manufacturer	Pass & Seymour/Legrand
Description	Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These Switches Offer Excellent Value While Meeting Federal Specification Standards. External Screw-Pressure-Plate Back Wiring Enables Fast Installation and Superior Electrical Connections. Rugged Construction Shrugs Off Hard Use and Abuse.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Three pole
actuator	Toggle
amperage rating	20
connection	Side Wire or external screw-pressure plate
Connection Type	Wired
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Fluorescent, LED, Xenon, Universal, Incandescent, CFL, Halogen
Material	Thermoplastic
media	Yes
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9172 E Florentine Road Unit 9  
86314-0000, AZ Prescott Valley  
Phone: 928-356-1174  
Fax: 480-426-8084

## Descriptions

Description	20A 120/277VAC S WIRE COMM 3W SW I
extra long description	P&S CS20AC3I 20A 120/277VAC S WIRE
Features	Single Piece Plated Steel Mounting Strap
Long Description	Commercial 3-Way Switch, Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse.
Product Type	20A 120/277VAC S Wire Comm 3W SW I
Special Features	Side wire, locking support, heavy duty toggle

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007126532
Manufacturers Part Number	CS20AC3I
UPC	785007126532

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting	WALL
nema rating	WD-1 and WD-6
Operating Temperature	-40°-115°F
standard	CULUS, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC