



Powering Business Worldwide

### 5262B

Recp Dup 15A125V 2P3W Const Grade B&S BR

UPC: 032664704277

### 5262BLS

Recp TVSS 15A 125V 2P3W Led & Alarm BL

UPC: 040893618869

### 5262BLSM

RecpTVSS 15A125V 2P3W Led&Alarm MOD BL

UPC: 032664674143

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (2) Toggle & Decorator

Special Features: Flush Fitting

Application: Residential/Commercial

Size: Standard, 4.56 In Width X 4.50 In Height

Gang: 2

Cutout: 1.31 In Width X 2.64 In Height

Material: Nylon

Thickness: 0.060 In

Color: Black

Mounting: Screw

Construction: Warp Resistant



Powering Business Worldwide

### 5262BM

RecpDup15A125V 2P3W ConstGrde B&S MOD BR

UPC: 032664704284

### 5262GY

Recp Dup 15A125V 2P3W Const Grade B&S GY

UPC: 032664704291

### 5262GYM

RecpDup15A125V 2P3W ConstGrde B&S MOD GY

UPC: 032664704307

Brand Name: Cooper Wiring Devices

Sub Brand: Arrow Hart

Type: Double Pole Switch

Special Features: Wiring Type Side Wire

Application: Commercial

Voltage Rating: 120/277 Vac

Amperage Rating: 15 Amp

Number Of Poles: 2

Connection: Screw

Actuator: Compact Toggle

Color: Black



Powering Business Worldwide

### 5262GYS

Recp TVSS 15A 125V 2P3W Led & Alarm GY

UPC: 040893619293

Brand Name: Cooper Wiring Devices  
Sub Brand: Arrow Hart  
Type: Double Pole Switch  
Special Features: Wiring Type Side Wire  
Application: Commercial  
Voltage Rating: 120/277 Vac  
Amperage Rating: 20 Amp  
Number Of Poles: 2  
Connection: Screw  
Actuator: Compact Toggle  
Color: Black

### 5262GYSM

RecpTVSS15A125V 2P3W Led&Alarm MOD GY

UPC: 032664674174

Brand Name: Cooper Wiring Devices  
Sub Brand: ARROW HART  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Back and Side Wire  
Application: Commercial  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Material: Nylon Face, PVC Base  
Color: Almond  
NEMA Rating: 5-15R  
Connection: Screw

### 5262LAM

RecpDup15A125V 2P3W ConstGrde B&S MOD LA

UPC: 032664704321

Brand Name: Cooper Wiring Devices  
Sub Brand: ARROW HART  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Back and Side Wire  
Application: Commercial  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Material: Nylon Face, PVC Base  
Color: Black  
NEMA Rating: 5-15R  
Connection: Screw



Powering Business Worldwide

### 5262V

Recp Dup 15A125V 2P3W Const Grade B&S IV

UPC: 032664704338

Brand Name: Cooper Wiring Devices  
Sub Brand: ARROW HART  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Back and Side Wire  
Application: Commercial  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 15 Amp  
Voltage Rating: 125 Vac  
Material: Nylon Face, PVC Base  
Color: Light Almond  
NEMA Rating: 5-15R  
Connection: Screw

### 5262VM

RecpDup15A125V 2P3W ConstGrde B&S MOD IV

UPC: 032664704345

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Back and Side Wire  
Application: Commercial grade  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 20 Amp  
Voltage Rating: 125 Vac  
Material: Nylon Face, PVC Base  
Color: Almond  
NEMA Rating: 5-20R  
Mounting: Flush  
Connection: Screw  
Size: 0.82 In Depth X 4.19 In Height  
Environmental Conditions: Indoor  
Dielectric Strength: 2000 V  
Insulation: Nylon Face, PVC Base  
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

### 5262VS

Recp TVSS 15A 125V 2P3W Led & Alarm IV

UPC: 040893618876

Brand Name: Eaton  
Sub Brand: ARROW HART  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Back and Side Wire  
Application: Commercial grade  
Standard: UL  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 20 Amp  
Voltage Rating: 125 Vac  
Material: Nylon Face, PVC Base  
Color: Black  
NEMA Rating: 5-20R  
Mounting: Flush  
Connection: Screw  
Size: 0.82 In Depth X 4.19 In Height  
Environmental Conditions: Indoor  
Dielectric Strength: 2000 V  
Insulation: Nylon Face, PVC Base  
Temperature Rating: -20C to 70C (-4F to 158F)

### 5262VSM

RecpTVSS 15A125V 2P3W Led&Alarm MOD IV

UPC: 032664676819

Brand Name: Cooper Wiring Devices  
Sub Brand: ARROW HART  
Type: Duplex, Straight Blade  
Special Features: Wiring Type Back and Side Wire  
Application: Commercial  
Number Of Poles: 2  
Number Of Wires: 3  
Wire Size: 14 To 10 AWG  
Amperage Rating: 20 Amp  
Voltage Rating: 125 Vac  
Material: Nylon Face, PVC Base  
Color: Light Almond  
NEMA Rating: 5-20R  
Connection: Screw



Powering Business Worldwide

### 5262W

Recp Dup 15A125V 2P3W Const Grade B&S WH

UPC: 032664704352

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Blank

Special Features: Standard Grade, Flush Fitting

Application: Residential

Size: Standard, 2.75 In Width X 4.50 In Height

Gang: 1

Cutout: 1.37 In Length X 3.25 Width

Material: Thermoset

Thickness: 0.080 In

Color: Almond

Mounting: Screw, Box

Construction: Warp Resistant

### 5262WM

RecpDup15A125V 2P3W ConstGrde B&S MOD

UPC: 032664704369

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (1) Single Receptacle

Special Features: Standard Grade, Flush Fitting

Application: Residential

Size: Standard, 2.75 In Width X 4.50 In Height

Gang: 1

Cutout: 1.406 In Diameter

Material: Thermoset

Thickness: 0.080 In

Color: Almond

Mounting: Screw

Construction: Warp Resistant

### 5262WS

Recp TVSS 15A 125V 2P3W Led & Alarm WH

UPC: 040893619149

Brand Name: Cooper Wiring Devices

Type: (2) Toggle Switch, (1) Decorator

Special Features: Standard Grade, Flush Fitting, Opening Configuration 0.40 In Width X 0.93 In Height, 1.31 In Width X 2.64 In Height

Application: Residential

Size: Standard, 6.37 In Width X 4.50 In Height

Gang: 3

Material: Thermoset

Thickness: 0.080 In

Color: Almond

Mounting: Screw

Construction: Warp Resistant



Powering Business Worldwide

**5262WSM**

RecpTVSS 15A125V 2P3W Led&Alarm MOD WH

UPC: 032664676826

Brand Name: Cooper Wiring Devices

Type: RJ11/RJ14 Telephone Jack

Size: 2.75 In Width X 4.50 In Height

Color: Almond

Mounting: Flush