

Eaton 5266NHG

Catalog Number: 5266NHG

Eaton Arrow Hart auto grip hospital grade straight blade plug, #18-12 AWG, 15A, Industrial, 125V, Back wire, Black and white, Brass, Nylon, 5-15P, Two-pole, three-wire, grounding, Screw, Nylon, Core pack



General specifications

Product Name	Catalog Number
Eaton Arrow Hart auto grip hospital grade straight blade plug	5266NHG
	UPC
	040893017709
Product Length/Depth	Product Height
1.91 in	4.13 in
Product Width	Product Weight
1.78 in	0.181 lb
Warranty	Compliances
Refer to warranty document.	RoHS Compliant
Certifications	
cULus Listed	
Federal Specification Classification 6221	
02	

Product specifications

Device type

Plug

Color

White

Black

Face/body material

Nylon

Wiring method

Back wire

Material

Nylon

Allowable wire size

#18-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Plug

Device grade

Extra heavy-duty hospital grade

NEMA configuration

5-15P

Style type

Straight body

Design type

Straight blade

Connection type

Screw

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 5266NHG](#)

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

Core pack



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)