

Ionization Smoke & Fire Alarm

120 Volt AC Hardwired with Battery Backup

Model 5304

Model 5304L (10 Year Lithium Battery)



Perfect for new or replacement installations, this 120 volt AC/DC hardwired smoke and fire alarm offers time-saving installation features, value and quality. This alarm is fully interconnectable with all USI and Universal brand alarms.

Features

Benefits

| | |
|---------------------------------------|--|
| Quick Find® alarm origination feature | Patented feature easily identifies first alarm to sound in an interconnected system |
| Quick activation battery pull tab | Preserve battery life. Preinstalled battery is quickly activated without removing alarm from bracket |
| Universal mounting bracket | Fits any standard wiring junction box, single gang, round or octagon, up to 4" |
| Quick connect wiring harness | Longer 8" pigtail wires are pre-stripped |
| Larger mounting base | Covers drywall imperfections and old paint marks |
| Interconnectable | With all USI and Universal brand 120V alarm using existing wiring & mounting |
| Front-load battery drawer | Replace battery without removing alarm from bracket |
| Single silence/test button | Temporarily quiets nonemergency alarms and tests alarm functionality |
| Full-size plastic dust cover | Protects alarm from dust, debris and painting during construction or home remodeling |
| 2 tamper resistant locking features | Prevents unauthorized alarm or battery removal |
| 10-year lithium battery backup | Provides power for the life of the alarm--Model 5304L only |

Technical Specifications

| | |
|--------------------|----------------------------------|
| Sensor Type: | Dual Ionization Sensing Chamber |
| Primary Power: | 120 Volt AC 60Hz |
| Battery Backup: | 9 Volt super heavy duty battery |
| Audible Alarm: | 85 dB at 10 feet |
| Temperature Range: | 40° F to 100° F (4° C to 38° C) |
| Humidity Range: | 5% to 95% RH |
| Interconnect: | Maximum 24 USI/Universal devices |
| LED: | Green=AC power, Red=alarm |
| Size: | 5.63" x 5.63" x 1.75" |
| Warranty: | 10 year limited |

Regulatory Compliance:

Underwriters Laboratories (UL-US)
 Underwriters Laboratories Canada (ULC)
 California State Fire Marshal (CSFM)
 National Fire Protection Association (NFPA)
 Housing and Urban Development (HUD)
 Federal Housing Authority (FHA)
 UTGT / UTHA



| MODEL | BRAND | Box | | SHELF PACK (in.) | | WEIGHT | | MASTER CTN (in.) | | WEIGHT | |
|-------|-------|------|-----|--------------------|-----------|-----------------|----------|----------------------|-----------|--------------------|---------|
| | | Clam | QTY | L x W x H | L x W x H | (Lbs.) | UPC CODE | QTY | L x W x H | (Lbs.) | I2 of 5 |
| 5304 | USI | BX | 1 | 5.75 x 5.75 x 1.75 | 0.42 | 0-42741-05304-4 | 12 | 12.00 x 12.00 x 6.13 | 8.55 | 1-00-42741-05304-1 | |
| 5304L | USI | BX | 1 | 5.75 x 5.75 x 1.75 | 0.42 | 0-42741-15304-1 | 6 | 12.00 x 6.38 x 6.38 | 4.55 | 1-00-42741-15304-8 | |

Ionization Smoke & Fire Alarm

120 Volt AC Hardwired with Battery Backup

Model 5304

Model 5304L (10 Year Lithium Battery)



Perfect for new or replacement installations, this 120 volt AC/DC hardwired smoke and fire alarm offers time-saving installation features, value and quality. This alarm is fully interconnectable with all USI and Universal brand alarms.

Features

Benefits

| | |
|---------------------------------------|--|
| Quick Find® alarm origination feature | Patented feature easily identifies first alarm to sound in an interconnected system |
| Quick activation battery pull tab | Preserve battery life. Preinstalled battery is quickly activated without removing alarm from bracket |
| Universal mounting bracket | Fits any standard wiring junction box, single gang, round or octagon, up to 4" |
| Quick connect wiring harness | Longer 8" pigtail wires are pre-stripped |
| Larger mounting base | Covers drywall imperfections and old paint marks |
| Interconnectable | With all USI and Universal brand 120V alarm using existing wiring & mounting |
| Front-load battery drawer | Replace battery without removing alarm from bracket |
| Single silence/test button | Temporarily quiets nonemergency alarms and tests alarm functionality |
| Full-size plastic dust cover | Protects alarm from dust, debris and painting during construction or home remodeling |
| 2 tamper resistant locking features | Prevents unauthorized alarm or battery removal |
| 10-year lithium battery backup | Provides power for the life of the alarm--Model 5304L only |

Technical Specifications

| | |
|--------------------|----------------------------------|
| Sensor Type: | Dual Ionization Sensing Chamber |
| Primary Power: | 120 Volt AC 60Hz |
| Battery Backup: | 9 Volt super heavy duty battery |
| Audible Alarm: | 85 dB at 10 feet |
| Temperature Range: | 40° F to 100° F (4° C to 38° C) |
| Humidity Range: | 5% to 95% RH |
| Interconnect: | Maximum 24 USI/Universal devices |
| LED: | Green=AC power, Red=alarm |
| Size: | 5.63" x 5.63" x 1.75" |
| Warranty: | 10 year limited |

Regulatory Compliance:

Underwriters Laboratories (UL-US)
 Underwriters Laboratories Canada (ULC)
 California State Fire Marshal (CSFM)
 National Fire Protection Association (NFPA)
 Housing and Urban Development (HUD)
 Federal Housing Authority (FHA)
 UTGT / UTHA



| MODEL | BRAND | Box Clam | QTY | SHELF PACK (in.) L x W x H | WEIGHT (Lbs.) | UPC CODE | QTY | MASTER CTN (in.) L x W x H | WEIGHT (Lbs.) | I2 of 5 |
|-------|-------|----------|-----|----------------------------|---------------|-----------------|-----|----------------------------|---------------|--------------------|
| 5304 | USI | BX | 1 | 5.75 x 5.75 x 1.75 | 0.42 | 0-42741-05304-4 | 12 | 12.00 x 12.00 x 6.13 | 8.55 | 1-00-42741-05304-1 |
| 5304L | USI | BX | 1 | 5.75 x 5.75 x 1.75 | 0.42 | 0-42741-15304-1 | 6 | 12.00 x 6.38 x 6.38 | 4.55 | 1-00-42741-15304-8 |