



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



531 Beamclamp 1/4-20 Tapped

Crouse-Hinds

Catalog Number	531
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Rigid/Imc Beam Clamp/Insulator Support, 1" Base Size, 3/4" Jaw Opening Size, Malleable Iron, 1/4"-20 Tapped Holes
Weight per unit	0.1800 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	1.2500 IN X 1.1900 IN X 1.3900 IN
Material	Malleable Iron

Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

Dimensions and Weight

Size	1 in
------	------

Descriptions

Description	BEAMCLAMP 1/4-20 TAPPED
extra long description	MIDWEST 531 1 BEAM CLMP 1/4 20
Features	Crouse-Hinds series clamps, straps, clampbacks and hangers are used to secure rigid/IMC conduit to mounting surfaces or to provide space between conduit and its mounting surfaces. Available in a variety of materials to meet customer preferences, including steel, malleable iron, stainless steel and hot dip galvanized iron.
Long Description	Eaton Crouse-Hinds series rigid/IMC beam clamp/insulator support, 1" base size, 3/4" jaw opening size, Malleable iron, 1/4"-20 tapped holes
Product Type	1 Beam CLMP 1/4 20
Special Features	Jaw Opening Size 3/4 In, Load Capacity 230 Lb, Weight 24 Lb per 100

Manufacturer Information

Brand	Eaton
GTIN	00784564105318
UPC	784564105318

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Beam clamp/insulator support



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	25
Weight Per each	0.18

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL, cUL