



## HEAVY-DUTY SPEC GRADE SINGLE RECEPTACLES, SIDE WIRE, 20A, 125V, LIGHT ALMOND

5351LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

#### Heavy-Duty Spec Grade Single Receptacle Side Wire 20amp 125volt Light Almond

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate side wire capability.
- One-piece brass triple-wire power contacts for lasting retention.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Single Receptacles  
Duty: Heavy Duty  
Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### DIMENSIONS

Depth (US): 1.08"  
Height (US): 3.28"  
Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 20A

Volts: 125V  
Volts (AC): 125  
Capacity: Single  
Grade Type: Federal Specification

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant





## HEAVY-DUTY SPEC GRADE SINGLE RECEPTACLES, SIDE WIRE, 20A, 125V, LIGHT ALMOND

5351LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

#### Heavy-Duty Spec Grade Single Receptacle Side Wire 20amp 125volt Light Almond

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate side wire capability.
- One-piece brass triple-wire power contacts for lasting retention.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Single Receptacles  
Duty: Heavy Duty  
Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### DIMENSIONS

Depth (US): 1.08"  
Height (US): 3.28"  
Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 20A

Volts: 125V  
Volts (AC): 125  
Capacity: Single  
Grade Type: Federal Specification

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

