




TWO GANG EXTENSION & THREE GANG BOX

2-5/8 in. Deep with Lugs - Seven Threaded Outlets - 4-1/2 in. x 6-3/8 in.
N/A

D07.1



Catalog #: 5390-0

APPLICATIONS

For use in branch circuit wiring in wet, damp, or dry locations
May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

PRODUCT FEATURES

- Reinforced connector outlets
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Eight box mounting options with detachable lugs
- Four closure plugs included
- Hubs accept all threaded fittings and threaded conduit
- Ground screw installed
- Multi-lingual instructions in each package
- Includes gasket and mounting hardware
- N/A

UL LISTED

File E195978

CSA

C22.2 No. 18

NEMA

3R Rated

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Number Of Outlets: 7
Gangs: 3

PRODUCT MEASUREMENTS

Depth: 2-5/8 in.
Outlet Size: 3/4 in.
Cubic Inches (cm3): 55.0 (901.3)
Wt. Ea. (Lbs.): 1.550

PACKAGING


Package Type: Boxed
Std. Pkg.: 1
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 155.00
Ship Carton Length (in.): 9.25
Ship Carton Width (in.): 5.75
Ship Carton Height (in.): 5.00
Ctn Weight (Lbs.): 1.55
Pallet Qty: 200.00
UPC Number: 050169539002
I2of5: 50050169539007



TWO GANG EXTENSION & THREE GANG BOX

2-5/8 in. Deep with Lugs - Seven Threaded Outlets - 4-1/2 in. x 6-3/8 in.
N/A

D07.1



Catalog #: 5390-0

APPLICATIONS

For use in branch circuit wiring in wet, damp, or dry locations
May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

PRODUCT FEATURES

- Reinforced connector outlets
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Eight box mounting options with detachable lugs
- Four closure plugs included
- Hubs accept all threaded fittings and threaded conduit
- Ground screw installed
- Multi-lingual instructions in each package
- Includes gasket and mounting hardware
- N/A

UL LISTED

File E195978

CSA

C22.2 No. 18

NEMA

3R Rated

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Number Of Outlets: 7
Gangs: 3

PRODUCT MEASUREMENTS

Depth: 2-5/8 in.
Outlet Size: 3/4 in.
Cubic Inches (cm3): 55.0 (901.3)
Wt. Ea. (Lbs.): 1.550

PACKAGING

Package Type: Boxed
Std. Pkg.: 1
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 155.00
Ship Carton Length (in.): 9.25
Ship Carton Width (in.): 5.75
Ship Carton Height (in.): 5.00
Ctn Weight (Lbs.): 1.55
Pallet Qty: 200.00
UPC Number: 050169539002
I2of5: 50050169539007