



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5466X Straight Blade Plug 3W 20A 250V B&W

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 5466X |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Plug 2-Pole 3-Wire 20A 250V |
| Weight per unit | 0.1400 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|----------------|
| amperage rating | 20 |
| connection | Wire Grounding |
| Material | Nylon |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage | 250.0 V |
| Voltage Rating | 250 |
| Wire Size | 4 |

Dimensions and Weight

| | |
|------|--------|
| Size | 2.8 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | STRAIGHT BLADE PLUG 3W 20A 250V B&W |
| extra long description | P&S PS5466X STR BLD PLUG 3W 20A 250 |
| Long Description | Straight Blade Plug 2-Pole 3-Wire 20A 250V |
| Product Type | STR BLD Plug 3W 20A 250V B&W |
| Special Features | Chemical & Impact resistant, 2pc cord grip accepts wide cord |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007237078 |
| Manufacturers Part Number | PS5466X |
| UPC | 785007237078 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | Straight Blade |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.14 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Extra Hard Use |
| nema rating | 6-20P |
| standard | CULUS, UL 498, FEDSPEC |