



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



54807 2AWG 2WAY Cop Conn

Abb Installation Products, Inc

Catalog Number	54807
Manufacturer	Abb Installation Products, Inc
Description	Copper Two-Way Splice, Long Barrel, Max 35KV, Wire Size #2 Awg, Length 1.88 Inches, Diameter 0.43 Inches, Tin Plated, Die Code 33, Die Color Code Brown
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V

Material, Color, and Finish

Color	Brown
Finish	Tin-Plated

Descriptions

Description	2AWG 2WAY COP CONN
extra long description	ABB 54807 2WAY CU SPLICE CONN LNGBR
Long Description	Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size #2 AWG, Length 1.88 Inches, Diameter 0.43 Inches, Tin Plated, Die Code 33, Die Color Code Brown
Product Type	2WAY Cu Splice Conn LNGBRL NO2 BRN
Special Features	Two-Way Connectors Provide High Pullout Values, are Easy to Insulate and Provide a Low-Resistance Connection of High Quality and Low Installed Cost

Manufacturer Information

Brand	COLOR-KEYED
GTIN	00786210548074
Manufacturers Part Number	54807
UPC	786210548074

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Splice Connector

Packaging

Carton	25
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Applications certified to 600 V and recommended up to 35 kV
standard	UL E9809 / UL E9809