



# SAM™ CL-3L

## Low-VOC PVC, CPVC, ABS Cleaner

[Description](#) | [Characteristics](#) | [Applications](#) | [Packaging](#) | [Instructions](#) | [Precautions](#) | [Specifications](#) | [Limited Warranty](#)

### DESCRIPTION:

---

Sam™ CL-3L is a clear cleaner for use on all PVC, CPVC and ABS pipe, tubing, and socket-type fittings. Max VOC per SCAQMD 1168/316A or BAAQMD Method 40: 550 g/l.

[Top of Page](#)

### CHARACTERISTICS:

---

- Safe for use on potable water systems
- Acts as a cleaner by dissolving grease and dirt and helping prepare the bonding surfaces for solvent cementing
- Helps make a clean, professional looking joint
- Good for PVC, CPVC and ABS systems
- LEED Compliant

[Top of Page](#)

### APPLICATIONS:

---

Sam™ CL-3L is specifically formulated as a cleaner for use on all PVC, CPVC, and ABS pipe applications such as potable water, pressure pipe, gas, conduit, and drain, waste and vent (DWV). It is for use with all sizes and classes in both Schedule 40 and Schedule 80.

[Top of Page](#)

### PACKAGING:

---

Code	Size	Qty. Per Case	Lbs. per Case	Cu. Ft Per Case
55929	1/4 pint dauber top (118 ml)	24 cans	10	.18
55930	1/2 pint dauber top (237 ml)	24 cans	16	.45
55932	Pint dauber top (473 ml)	12 cans	15	.43
55934	Quart dauber top (946 ml)	12 cans	28	.78
55936	Gallon can (3.8 L)	4 cans	34	.80

[Top of Page](#)

### **INSTRUCTIONS:**

1. Store and apply between 40 degree F and 120 degree F. Use below 40 degree F only with proper solvent cement and with extreme care.
2. **Wear non-permeable gloves during application to avoid skin contact.**
3. Cut pipe end square and remove ragged edges and burrs. Clean fitting socket and pipe, and check for proper fit.
4. Using supplied dauber applicator, apply CLEANER evenly and freely to socket and then to pipe end for length of socket depth. Then apply again to socket. Avoid puddling. For pipe greater than 2" diameter use natural-bristle sized to 1/2 of the pipe diameter.
5. Temperature and humidity conditions may require repeated applications to one or both surfaces to avoid drying. While still wet, quickly apply proper solvent cement and make up pipe joint in accordance with cement's instructions.

For additional technical information, call Toll Free 1-800-231-3345.

[Top of Page](#)

### **PRECAUTIONS:**

FOR CHEMICAL EMERGENCY, SPILL, LEAK, FIRE, EXPOSURE OR ACCIDENT,

CALL CHEMTREC - DAY OR NIGHT 1-800-424-9300

**D A N G E R!**

EXTREMELY FLAMMABLE • HARMFUL OR FATAL IF SWALLOWED  
 VAPOR HARMFUL • EYE AND SKIN IRRITANT • MAY BE ABSORBED THROUGH  
 SKIN  
 VAPORS MAY CAUSE FLASH FIRES

**CONTAINS:** Methyl Ethyl Ketone and Acetone. **PRECAUTIONS:** Vapors are heavier than air and can collect in low areas. Keep away from heat, sparks, and flames until vapors are gone. Use only with good cross-ventilation. Wear adequate protective gear and clothing. Avoid breathing vapors and contact with skin, eyes and clothing. Long term repeated overexposure to solvents may cause damage to the brain, nervous system, reproductive system, respiratory system, mucous membranes, liver, and kidneys. Wash after handling. **FIRST AID:** For any overexposure, get immediate medical attention after first aid is given. **Eyes** - Flush 15 minutes with clean water. **Skin** - Wash with soap and water. **Inhalation** - Remove to fresh air. **Ingestion** - DO NOT INDUCE VOMITING. Only if conscious, give large amounts of water. Do not reuse empty container. **KEEP OUT OF REACH OF CHILDREN.**

For additional information, refer to Material Safety Data Sheet.

[Top of Page](#)

**SPECIFICATIONS:**

---

Wt/Gal @ 77 degree F	6.9+- .2 lbs/gal.
Flash Point SETA CC	4.1 degree F
Color	Clear
Shelf Life	2 years minimum, Subject to inspection



Suggestions and recommendations covering the use of our products are based on our past experience and laboratory findings. However, as we have no control as to the methods and conditions of application, we only assume responsibility for the uniformity of our products within manufacturing tolerances.

[Top of Page](#)

**LIMITED WARRANTY:**

---

RectorSeal® makes the Limited Express Warranty that when the instructions for storage and handling of our products are followed we warrant our products to be free from defects. THIS LIMITED EXPRESS WARRANTY IS EXPRESSLY IN LIEU OF ANY OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, AND OF ANY OTHER OBLIGATION ON THE PART OF RECTORSEAL®. The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and RectorSeal® shall not be liable for incidental or consequential damages.

[Top of Page](#)

## **RectorSeal®**

2601 Spenwick Drive • Houston, TX 77055 USA

713-263-8001 • Fax 713-263-7577

Toll-free 800-231-3345 • Fax 800-441-0051

F-10

[Back to Solvent Cements](#)