



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5662 Recp Dup 15A 250V S+B Wire BN

*Pass & Seymour/Legrand*

Catalog Number	5662
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 15 A, 250 V Ac, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back and Side Wired Connection, Wall Mount, 1.322 In Length, 0.780 In Width, 3.281 In Height, Nylon Material, Brown, 0.2100 LB
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
Poles	Double Pole
Voltage	250.0 V
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Descriptions

Description	RECP DUP 15A 250V S+B WIRE BN
extra long description	P&S 5662 RECP DUP 15A 250V S+B WIRE

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007566208
UPC	785007566208

### Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Spec Grade Receptacle, Heavy-Duty

### Trade Size

Amperage	15.0
----------	------

### Packaging

Carton	10
Package	100
Weight Per each	0.2083

### Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
standard	FEDSPEC, CULUS, cULus UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C