



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



567 Scotchlok Electrical Idc 567-Pouch, BR *Minnesota Mining (3M)*

Catalog Number	567
Manufacturer	Minnesota Mining (3M)
Description	3M™ Scotchlok™ Insulation Displacement Connector 567 Electrically Connects A Tap Wire to A Run (Through) Wire While Insulating The Connection. This Connector Is Suitable For Control Circuit Wiring, Fixture Wiring, Appliance Wiring, Signal and Pa Systems and Automotive/Boat/RV Wiring. Polypropylene Insulated and Self Stripping.
Weight per unit	0.0008 (lbs/each)
Product Category	Small Terminals & Connectors

Descriptions

Description	SCOTCHLOK ELECTRICAL IDC 567-POUCH, BR
extra long description	3M 7100167058 3M™ Scotchlok™ IDC C
Features	3M™ Scotchlok™ Insulation Displacement Connector 567 is 600V rated for building wire and 1000V rated for signs, fixtures and luminaires. The connector withstands temperatures of 221 degrees F (105 degrees C). UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.
Long Description	3M™ Scotchlok™ Insulation Displacement Connector 567 electrically connects a tap wire to a run (through) wire while insulating the connection. This connector is suitable for control circuit wiring, fixture wiring, appliance wiring, signal and PA systems and automotive/boat/RV wiring. Polypropylene insulated and self stripping.
Product Type	3M™ Scotchlok™ Idc Connector 567
Special Features	Flame Retardant

Manufacturer Information

Brand	Scotchlok
GTIN	00054007148876
Manufacturers Part Number	567POUCH
UPC	054007148876

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Insulation Displacement

Availability

minimum qty	100
-------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Package	1000
Weight Per each	0.0008

Uses, Certifications, and Standards

standard	UL and CSA
----------	------------