



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5871 SGL Recp 20A 250V S+B Wire BR

Pass & Seymour/Legrand

Catalog Number	5871
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Spec Grade Single Receptacle Back and Side Wire 20A 250V
Weight per unit	0.1802 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Commercial, Indoor
Poles	Double Pole
Voltage	250.0 V
Voltage Rating	250
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Color	Brown
-------	-------

Dimensions and Weight

Height	3.68
Width	1.093

Descriptions

Description	20A 250V STRAIGHT BLADE SGL RCPT 620R
extra long description	P&S 5871 RECP SGL 20A 250V S+B WIRE
Long Description	Heavy-Duty Spec Grade Single Receptacle Back and Side Wire 20A 250V
Product Type	Recp SGL 20A 250V S+B Wire BN
Special Features	Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. One-piece brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for pos



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007587104
Manufacturers Part Number	5871
UPC	785007587104

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	10
Package	100
Weight Per each	0.1802

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	6-20R
standard	CUL, FEDSPEC, CULUS, UL498, CSA C22.2 No. 42, FEDSPEC
Temperature Rating	-40° - 60° C