

Heavy-Duty Spec Grade Single Receptacles, Back & Side Wire, 20A, 250V, Brown

5871



Heavy-Duty Spec Grade Single Receptacle
Back & Side Wire 20amp 250volt Brown



features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

specifications

General Info

Color: brown
Type: Single,Receptacles
Duty: Heavy Duty
Special Features: Back,Side Wire

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42
CSA Standard: Yes

Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406
UR: No

Dimensions

Depth U S: 1.093"
Height U S: 3.28"
Width U S: 1.32"

Technical Information

Amps: 20 Amp
Volts: 250V
Volts A C: 250
Capacity: Single
Grade Type: Federal Specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant