

LEE ELECTRIC INC

TRANSFORMER 592 CLASS 2 SIGNALING TRANSFORMER

FEATURES

NON-REGENERATIVE THERMAL OVERLOAD PROTECTION

GROUNDING WIRE

PRE STRIPPED PIG TAILS

SCREW TERMINAL CONNECTION ON SECONDARY

DESCRIPTION

LEE ELECTRIC 592 CLASS 2 SIGNALING TRANSFORMER IS EASY TO INSTALL, LOW VOLTAGE POWER SOURCES FOR RESIDENTIAL, COMMERCIAL AND INDUSTRIAL USES

AGENCY APPROVAL

UL

SPECIFICATIONS

120 VOLT AC INPUT

SECONDARY OUTPUT (8 VOLT AC 10 VA ; 16 VOLT AC 10 VA; 24 VOLT AC 20 VA)

INSTALLATION

MOUNTS IN A STANDARD ½" KNOCKOUT OR SURFACE MOUNTS USING THE PROVIDED FOOT MOUNTS. THE TRANSFORMER IS SUITABLE FOR MOUNTING IN BOTH PLASTIC AND METAL BACK BOXES.

APPLICATION

THE LEE ELECTRIC 592 TRANSFORMER ARE USED IN LIGHT DUTY APPLICATIONS. THEY ARE IDEAL FOR STANDARD DOORBELLS AND CHIMES IN RESIDENTIAL AND COMMERCIAL APPLICATIONS (NOTE...FOR HIGHER POWER REQUIREMENTS IT IS RECOMMENDED TO USE THE 598 TRANSFORMER WHICH OFFERS A SECONDARY OUTPUT OF 8 VOLT AC 20 VA; 16 VOLT AC & 24 VOLT AC 30 VA)

