

Eaton 5PX1500RTG2

Catalog Number: 5PX1500RTG2

Eaton 5PX G2 UPS, 2U, 1440 VA, 1440 W, 5-15P input, Outputs:
(8) 5-15R, 120V

General specifications



Photo is representative

Product Name
Eaton 5PX G2 UPS

Catalog Number
5PX1500RTG2

UPC
743172105776

Product Length/Depth
17.6 in

Product Height
3.4 in

Product Width
17.2 in

Product Weight
50.7 lb

Warranty
3 year on electronics, 3 year on batteries
with registration

Compliances

CE Marked
REACH

Certifications

CULus
RoHS
NOM
ENERGY STAR certified
IEC 62040-1

Battery

Runtime graph

View runtime graph

Battery management

ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)

Battery replacement

User replaceable

Battery type

Sealed, lead-acid

Extended battery capability

Add up to 4 extended battery modules (EBM). Part number 5PXEBM48RTG2

Electrical output

Receptacle

(8) 5-15R

Topology

Line-interactive

Wattage

1440 W

VA rating

1440 VA

Electrical input

Input connection

5-15P

Input cord length

10 ft

Input nominal voltage

120V

Nominal frequency

50/60 Hz

Input power factor

1

Communications

Expansion slots

One slot

Software compatibility

Brightlayer Data Centers suite

User interface

LCD graphical display

Environmental

BTU Rating

Online: 106, Battery: 699

Additional specifications

Special features

UPS ship-in-rack option for integration into packaged deployments simplifying set up and getting you online quicker (available with the RK4PRS 4-post rail kit)

Form factor

Rack/tower

Rack size

2U

Efficiency

98%

Package contents

5PX1500RTG2 UPS
Tower pedestal feet
Four-post rail kit
Quick start guide
Safety guide
USB cable
RS-232 cable

Warranty and support

Standard factory warranty

3-year factory warranty with
registration
-3 years
-Parts, electronics and
batteries coverage
-Standard ground shipping
-Technical support

Extended service plans

ADVANCED DEPOT
EXCHANGE
-5-YEAR DEPOT REPAIR:
5SW5Y-1750UC
-Expedited parts coverage
for 5 years
-Parts, electronics and UPS
batteries coverage
-Next business day shipping
-Technical support
ON-SITE 24X7, NEXT DAY
RESPONSE
2 YEAR UPGRADE:
WUN72XXX-2509UC
-On-site expedited parts and
labor coverage for first 2
years
-Parts, electronics and UPS
batteries coverage
-Eaton on-site labor
coverage
-24x7 coverage, next day
response
-Next day shipping
-Technical support
3 YEAR FLEX PLAN:
FLN73XXX-2509UC
-On-site parts and labor
coverage for years 3 to 5
-Parts, electronics and UPS
batteries coverage
-24x7 on-site labor
coverage, next day
response
-Next day shipping

Resources

Brochures

[Eaton 5PX G2 UPS brochure](#)

Manuals and user guides

[Eaton 5PX G2 UPS quick start guide](#)

Specifications and datasheets

[Eaton Specification Sheet - 5PX1500RTG2](#)

Technical data sheets

[Eaton 5PX G2 UPS technical specifications](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)