




GE
Lighting

62704 - 60PARH1500FL25TP

GE energy-efficient halogen 60 watt PAR38 floodlight 1-pack

- GE energy-efficient halogen bulbs deliver crisp, white light. This unsurpassed light quality is ideal for adding depth, drama and interest to any room or outdoor space. These GE energy-efficient halogen floodlights use less energy than standard halogen bulbs, saving money on energy. GE energy-efficient halogen floodlights feature lenses designed to provide a precise beam pattern, dispensing broad beams of crisp, white light throughout your home. Use these bulbs in indoor track and recessed fixtures or outdoor security fixtures instead of regular incandescent and create a dramatic effect
- Estimated yearly energy costs \$7.23 based on 3 hours per day \$0.11 per kWh
- Lasts 1.4 years based on 3 hours per day usage
- PAR38 indoor/outdoor floodlight with medium base for use in outdoor security lighting and indoor directional fixtures



GENERAL CHARACTERISTICS

Lamp Type	Halogen - PAR
Bulb	PAR38
Base	Medium Screw (E26)
Filament	CC-8
Rated Life	1500.0 hrs
Base Material	Brass
Bulb Material	Borosilicate glass
Additional Info	Floodlight
Primary Application	Indoor Floodlight

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	1070.0
Center Beam Candlepower (CBCP)	4050.0
Color Temperature	2900.0 K
Color Rendering Index (CRI)	100.0
Beam Spread	25.0 °
Nominal Initial Lumens per Watt	17

ELECTRICAL CHARACTERISTICS

Wattage	60.0
Voltage	120.0
Burn Position	Universal burning position

DIMENSIONS

Maximum Overall Length (MOL)	5.3100 in(134.9 mm)
Bulb Diameter (DIA)	4.750 in(120.6 mm)

PRODUCT INFORMATION

Product Code	62704
Description	60PARH1500FL25TP
Standard Package	Case
Standard Package GTIN	10043168627044
Standard Package Quantity	6
Sales Unit	Pallet
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	43168627047