



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



61076 Vol-Con Solenoid Voltage Tester

Ideal

| | |
|------------------|---|
| Catalog Number | 61076 |
| Manufacturer | Ideal |
| Description | Ideal, Voltage/Continuity Tester, Vol-Con, Solenoid, Voltage Rating: 5V to 600V Ac/DC, Warranty: 2 Year |
| Weight per unit | 0.9500 (lbs/each) |
| Product Category | Testers & Accessories |

Features

| | |
|----------------|------------|
| Voltage Rating | 5V To 600V |
|----------------|------------|

Descriptions

| | |
|------------------------|---|
| Description | VOL-CON SOLENOID VOLTAGE TESTER |
| extra long description | IDEAL 61-076 VOL-CON TESTER |
| Features | Extremely rugged and reliableVibrates when AC voltage is presentIndicates AC/DC voltage levelReplaceable leads with shielded probe tips (IEC61010-031 compliant)Bright, long-life LEDs and neon indicator lampDual voltage indication for backup safety2-year warranty |
| Long Description | IDEAL, Voltage/Continuity Tester, Vol-Con, Solenoid, Voltage Rating: 5V To 600V AC/DC, Warranty: 2 year |
| Product Type | Vol-Con Tester |
| Special Features | Features: Extremely Rugged And Reliable Three-In-One Tester; Vibrates When Voltage Is Present; Tests For High Voltage Up To 600V AC/DC; Tests For Low Voltage As Low As 5V AC/DC; Automatic Switching Continuity Tester; Replaceable Leads With Shielded Probe Tips; Bright Long-Life LED And Neon Indicator Lamps; 2-Year Warranty; CAT III - 600V; Warranty: 2 year |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250610761 |
| Manufacturers Part Number | 61-076 |
| UPC | 783250610761 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | TEST EQUIPMENT, TESTERS AND MULTIMETERS |
| Type | Solenoid |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.95 |