

PIPE VISES & SUPPORTS

Pipe Vises



425 Portable TRISTAND Chain Vise

NEW

460-12 Portable TRISTAND Chain Vise



40-A Portable TRISTAND Yoke Vise

Portable TRISTAND® Vises

- Models 460 and 40-A include integral legs and tray folds in for easy carrying and setup. Large vise base overhangs front legs for clear tool swing.
- Models 460 and 40-A include slots for hanging tools, pipe rest, three-pipe benders and ceiling brace screw.
- Model 460-6 features a larger work surface, 6" (150 mm) diameter, rear support and receding ceiling brace screw.
- Model 460-12 features an integrated ground lug to provide a conductive surface to connect the weld ground.
- Model 425 features "quick grab" self-locking latch and carrying handle for ease of transport.

Catalog No.	Model No.	Description	Pipe Capacity		Weight		Std. Pack
			in.	mm	lb.	kg	
40130	40-A	Portable TRISTAND Yoke Vise	1/8 - 2 1/2	6 - 60	48 1/2	22,0	1
16703	425	Portable TRISTAND Chain Vise	1/8 - 2 1/2	6 - 60	32	14,5	1
36273	460-6	Portable TRISTAND Chain Vise	1/8 - 6	6 - 150	42 3/4	19,4	1
36278	460-12	Portable TRISTAND Chain Vise**	1/8 - 12	6 - 300	60 3/4	27,6	1

** For model 460-6, jaw for plastic pipe, Catalog No. 41280 available; order separately.

Top Screw Stand Chain Vise



Stand Chain Vise

- Handy, portable stand chain vise.
- Sturdy cast-iron frame.
- Equipped with pipe rest, pipe bender and tool tray. Pipe for legs and connecting pipe not furnished. Use 1 1/4" (32 mm) pipe for the front legs and the connecting piece and 1" (25 mm) pipe for the rear legs.

Catalog No.	Model No.	Description	Pipe Capacity		Weight		Std. Pack
			in.	mm	lb.	kg	
40165	560	Top Screw Stand Chain Vise	1/8 - 5	6 - 125	25 3/4	11,7	1

Top Screw Bench Chain Vise



Bench Chain Vises

- Crank handle is anchored to base.
- Rugged cast-iron base has handy pipe rest and bender. Capacities of 1/8" (6 mm) through 8" (200 mm).
- Two models available for plastic pipe. Toothless jaws are neoprene-coated to prevent scoring of pipe.

Catalog No.	Model No.	Description	Pipe Capacity		Weight		Std. Pack
			in.	mm	lb.	kg	
40185	BC210	Top Screw Bench Chain Vise	1/8 - 2 1/2	6 - 60	7 3/4	3,5	1
40195	BC410	Top Screw Bench Chain Vise	1/8 - 4	6 - 100	14 3/4	6,7	1
40190	BC210P	Top Screw Bench Chain Vise*	1/2 - 2 7/8 O.D.	15 - 70	7 3/4	3,5	1
40200	BC410P	Top Screw Bench Chain Vise*	1/2 - 4 1/2 O.D.	15 - 110	15	6,8	1
40205	BC510	Top Screw Bench Chain Vise	1/8 - 5	6 - 125	14 3/4	6,7	1
40210	BC610	Top Screw Bench Chain Vise	1/4 - 6	8 - 150	24 1/2	11,1	1
40215	BC810	Top Screw Bench Chain Vise	1/2 - 8	15 - 200	37 1/4	16,9	1
40175	BC2A	Bottom Screw Bench Chain Vise	1/8 - 2	6 - 50	6	2,7	1
40180	BC4A	Bottom Screw Bench Chain Vise	1/8 - 4	6 - 100	13 3/4	6	1

*For Plastic Pipe and Tube.

(TOOLTIP) TRISTAND® vises include an adjustable method to increase stand stiffness. Model 460-12 includes an adjustable rear leg to level the stand.