



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65033000 3/4" LFNC Orange Sealtite *Southwire Company*

Catalog Number	65033000
Manufacturer	Southwire Company
Description	Liquid Tight Sealtite, Orange Color, Made In Usa, 6503 Model/Series, LFNC Style, 3/4 In Trade Size, 0.18 LB/FT Weight
Weight per unit	0.1800 (lbs/each)
Product Category	Liquid Tight Conduit

Features

Inside Diameter	0.805/0.845
Material	PVC
outside diameter	1.140/1.180

Material, Color, and Finish

Finish	PVC
Jacket Material	PVC

Dimensions and Weight

Length	100
--------	-----

Descriptions

Description	3/4" LFNC ORANGE SEALTITE
extra long description	AFC 6503-30-00 3/4 UL ORANGE LFNC-A
Features	LIQUID-TUFF™ Type LFNC-A is a layered Liquidtight Flexible Nonmetallic Conduit, designed for use in wet, dry or oily locations as a flame resistant, Nonmetallic raceway for power, control and communications cables where repetitive motion and constant flexing is required. It is intended for applications where abrasion and physical abuse may occur. LIQUID-TUFF™ Type LFNC-A carries the UL Listing Marks for US and Canada
Special Features	Nylon reinforced braid between two layers of PVC for strength and flexibility. Sunlight resistant, oil resistant, mild acid resistance, non-conductive raceway.

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680175724
Manufacturers Part Number	6503-30-00
UPC	077680175724

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Non-Metallic Conduit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.18

Uses, Certifications, and Standards

Application	Constant flexing and motion applications
standard	UL 1660 E123464
Temperature Rating	176