

65/1081 n/a

Lighting Products

2FT LED CEILING WRAP

Lamp Type Lighting Products

Warranty 5 Year Limited



Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
65/1081	Lighting Products	*	n/a	n/a	n/a	n/a	n/a
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
n/a	n/a	n/a	n/a	4	Box	n/a	Yes

65/1081 n/a

Lighting Products

2FT LED CEILING WRAP

Lamp Type Lighting Products

Warranty 5 Year Limited



Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
65/1081	Lighting Products	*	n/a	n/a	n/a	n/a	n/a
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
n/a	n/a	n/a	n/a	n/a	n/a	n/a	n/a
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
n/a	n/a	n/a	n/a	4	Box	n/a	Yes