

Project Name

Location

Prepared By



NUVO 65-1084

4FT LED CEILING WRAP

Notes

[www] 01-20-2023 09:30:47

General

Status	Transitioning
Substitute	65-1211
Fixture Type	Ceiling Wrap
Finish	White
Wattage	40W
Lumen Output	3200L
CCT (Kelvin)	3000K
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Warm White
CRI	90
Voltage	100V-277V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Non-Dimmable
Weight (lb.)	4.47
Material	Steel

Dimensions

Height (in.)	2.63
Width (in.)	5.5
Length (in.)	47.5

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------