

Project Name

Location

Prepared By



**Notes**

[www] 10-11-2021 02:00:29

**General**

Status	Active
Fixture Type	Security Lighting
Finish	Black
Wattage	20W
Lumen Output	1900L
CCT (Kelvin)	4000
Temperature	Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

**Specifications**

Technology	LED
CRI	80
Voltage	120V
Beam Angle	50
Rated Hours	50000
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
Dimmable	Non-Dimmable
Photocell	Has Motion Sensor
Lens Material	Glass
Weight (lb.)	2.8
Material	Die Cast Aluminum

**Dimensions**

Width (in.)	4.16
Length (in.)	7.63

**Compliance**

Safety Listing	cULus
Location Rating	Wet
UL Application	Outdoor
Energy Star	Yes
ES Unique ID	ESID-2336405
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

**Additional Information**

Warranty	5 Year Limited - Fixtures
----------	---------------------------