

Project Name

Location

Prepared By



## NUVO 65-718

LED 2 BULLET HEAD SECURITY LGT

**Notes**

[www] 03-15-2021 00:27:50

**General**

Status	Active
Fixture Type	Security Lighting
Finish	Bronze
Wattage	20
Lumen Output	1900
CCT (Kelvin)	4000
Temperature	Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

**Specifications**

Technology	LED
CRI	80
Voltage	120V-277V
Beam Angle	50
Rated Hours	50000
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
Dimmable	Non-Dimmable
Photocell	No
Lens Material	Glass
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	2.41
Material	Die-Cast Aluminum

**Dimensions**

Height (in.)	4.54
Width (in.)	8.16
Extension (in.)	8.80

**Compliance**

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2367480
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

**Additional Information**

Warranty	5 Year Limited - Fixtures
----------	---------------------------