

Project Name

Location

Prepared By



NUVO 65-719

LED 2 BULLET HEAD SECURITY LGT

Notes

[www] 10-27-2025 05:20:02

General

| | |
|---------------------------|-------------------|
| Status | Active |
| Fixture Type | Security Lighting |
| Finish | Bronze |
| Wattage | 20W |
| Lumen Output | 1900L |
| CCT (Kelvin) | 4000K |
| Temperature | Cool White |
| IP Rating | IP65 |
| Indoor or Outdoor Fixture | Outdoor |

Specifications

| | |
|-----------------------|---------------------------------|
| Technology | LED |
| CRI | 80+ |
| Voltage | 120V |
| Beam Angle | 50 |
| Rated Hours | 50000 |
| Operating Temperature | -30C (-22F) to +50C (+122F) |
| Dimmable | Non-Dimmable |
| Photocell or Sensor | Has Photocell |
| Lens Material | Glass |
| Surge Protection | Built-in surge protection - 2KV |
| Weight (lb.) | 2.66 |
| Material | Die-Cast Aluminum |

Dimensions

| | |
|-----------------|------|
| Height (in.) | 6.42 |
| Width (in.) | 8.16 |
| Extension (in.) | 8.8 |

Compliance

| | |
|----------------------------|-------------------------------|
| Safety Listing | cETLus - Listed |
| Location Rating | Wet |
| ENERGY STAR | No |
| DLC Approved | No |
| ADA Compliant | No |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| Canadian Standard ICES-005 | Class A |
| SDS Sheet | LED_Fixture |

Additional Information

| | |
|--------------------|---------------------------------------|
| Specification Note | Adjustable Angle from 0 to 90 degrees |
| Warranty | 5-Years |

Project Name

Location

Prepared By



NUVO 65-719

LED 2 BULLET HEAD SECURITY LGT

Notes

[www] 10-27-2025 05:20:02

General

| | |
|---------------------------|-------------------|
| Status | Active |
| Fixture Type | Security Lighting |
| Finish | Bronze |
| Wattage | 20W |
| Lumen Output | 1900L |
| CCT (Kelvin) | 4000K |
| Temperature | Cool White |
| IP Rating | IP65 |
| Indoor or Outdoor Fixture | Outdoor |

Specifications

| | |
|-----------------------|---------------------------------|
| Technology | LED |
| CRI | 80+ |
| Voltage | 120V |
| Beam Angle | 50 |
| Rated Hours | 50000 |
| Operating Temperature | -30C (-22F) to +50C (+122F) |
| Dimmable | Non-Dimmable |
| Photocell or Sensor | Has Photocell |
| Lens Material | Glass |
| Surge Protection | Built-in surge protection - 2KV |
| Weight (lb.) | 2.66 |
| Material | Die-Cast Aluminum |

Dimensions

| | |
|-----------------|------|
| Height (in.) | 6.42 |
| Width (in.) | 8.16 |
| Extension (in.) | 8.8 |

Compliance

| | |
|----------------------------|-------------------------------|
| Safety Listing | cETLus - Listed |
| Location Rating | Wet |
| ENERGY STAR | No |
| DLC Approved | No |
| ADA Compliant | No |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| Canadian Standard ICES-005 | Class A |
| SDS Sheet | LED_Fixture |

Additional Information

| | |
|--------------------|---------------------------------------|
| Specification Note | Adjustable Angle from 0 to 90 degrees |
| Warranty | 5-Years |