



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65BEMWSWW590CRIM 6" 11W Led Recessed Trim 27/30/35/40/50K 900LM *Lithonia Lighting - Acuity*

Catalog Number	65BEMWSWW590CRIM
Manufacturer	Lithonia Lighting - Acuity
Description	The E Series Combines Dependable Performance and Low Cost With The Virtually Maintenance-Free, Energy-Saving Benefits At 50, 000 Hour Rated-Life Led. Ideal For Both Retrofitting and New Construction In A Variety Of Residential and Light Commercial Settings Such As Multifamily Residences, Retail Shops and Offices.
Weight per unit	0.7000 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	7.625 x 7.625 x 3.667
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1200 LM,900 LM
Material	Aluminum
Number of Lamps	1
Shape	Round
Voltage Rating	120 V
Warranty	5
Wattage	13.9

Material, Color, and Finish

Color	White
Finish	Matte
Style	CONTEMPORARY

Dimensions and Weight

Height	3.67
Length	7.63
Width	7.63



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Retrofit
Description	6" 11W LED RECESSED TRIM 27/30/35/40/50K 900LM
extra long description	LITH 65BEMW SWW5 90CRI M6 6IN Juno
Features	Contractor Select
Long Description	The E Series combines dependable performance and low cost with the virtually maintenance-free, energy-saving benefits at 50,000 hour rated-life LED. Ideal for both retrofitting and new construction in a variety of residential and light commercial settings such as multifamily residences, retail shops and offices.
Product Type	Trim

Manufacturer Information

Brand	JUNO
GTIN	00194994160564
Manufacturers Part Number	65BEMW SWW5 90CRI M6
UPC	194994160564

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Trim

Trade Size

aperture size	5 IN,6 IN
---------------	-----------

Packaging

Carton	1
Package	6
Weight Per each	0.7

Uses, Certifications, and Standards

Application	Hospitality,Residential,Retail,Retrofit
environmental conditions	Indoor,Outdoor
Mounting	Recessed
standard	CSAusCA Title 20,CA Title 24,ENERGY STAR,JA8