



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 6624GRTNK 6X6X24 N3R RT Wireway No Ko

Unity MFG

Catalog Number	6624GRTNK
Manufacturer	Unity MFG
Description	Slip-On Cover Trough, Slip On, Gray, Low Carbon Steel, 24 In Overall Length, 6 In Overall Height, 6 In Overall Width, Powder Coated, 11 LB
Weight per unit	11.0 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

### Features

Knockouts	NO
-----------	----

### Dimensions and Weight

Depth	6
Length	24
Width	6

### Descriptions

Description	6X6X24 N3R RT WIREWAY NO KO
extra long description	UNT 6624GRTNK N3R SCREW COVER GUTTE
Special Features	For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket

### Manufacturer Information

Brand	Unity
GTIN	00761515141908
UPC	761515141908

### Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	GRT Gutter Slip-On Cover Wiring Trough

### Packaging

Carton	1
Weight Per each	11

### Uses, Certifications, and Standards

Enclosure	NEMA 3R, IP32
standard	UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant