



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 693W Combo 2 Switches 3W 15A 120/277V WH

*Pass & Seymour/Legrand*

Catalog Number	693W
Manufacturer	Pass & Seymour/Legrand
Description	Double 3-Way Combination Switch, 15A, 120/277V
Weight per unit	0.2500 (lbs/each)
Product Category	Combination Devices

### Features

action	(2) 3W
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
operating cycles	30000
Poles	3-way
Voltage	0.433 V
Voltage Rating	0.433212996389892
Wattage	Electrical power is expressed in Amps and Volts.

### Material, Color, and Finish

Color	White
-------	-------

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2 SWITCHES 3W 15A 120/277V WH
extra long description	P&S 693WG COMBO 2 SWITCHES 3W 15A 1
Long Description	Double 3-way Combination Switch, 15A, 120/277V
Product Type	Combo 2 Switches 3W 15A 120/277V W
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007006155
Manufacturers Part Number	693WG
UPC	785007006155

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	COMBINATION



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 15.0

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.25

## Uses, Certifications, and Standards

Application ..... Residential/Commercial

environmental conditions ..... Flammability: UL94 V2

Mounting ..... WALL

Operating Temperature ..... Maximum continuous +60°C, minimum -30°C

standard ..... CULUS, UL20