

# Combination Switches

696G



Single Pole, Three-Way Combination  
Switch, 15 amps, 120/277 amps, Brown.

## features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.



## specifications

### General Info

Type: Combination, Double  
Number Of Poles: 1, 3-way

### Listing Agencies/Third Party Information

UL Listing No: 20  
UL Standard: Yes  
UN SPS C: 39121406

### Dimensions

Depth U S: 0.94"  
Height U S: 3.28"

Width U S: 1.32"

**Technical Information**

Amps: 16 Amp  
Volts: 120/277VAC  
Volts A C: 120/277

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant