

Non-Grounding Combination Switches

696I



Single Pole, Three-way Combination
Switch, 15 amps, 120/277 volts, Ivory.

features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.



specifications

General Info

Type: Combination, Double
Number Of Poles: 1, 3-way
Special Features: Non-Grounding

Listing Agencies/Third Party Information

UL Listing No: 20
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 0.94"
Height U S: 3.28"
Width U S: 1.32"

Technical Information

Amps: 16 Amp
Volts: 120/277VAC
Volts A C: 120/277

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant