



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7125ST 1-1/4 In Emt Comp Conn In *Appleton/Oz Gedney*

|                  |                                                                                                                                                                                                                                                              |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | 7125ST                                                                                                                                                                                                                                                       |
| Manufacturer     | Appleton/Oz Gedney                                                                                                                                                                                                                                           |
| Description      | Features:1 13/16IN Dia X 2IN Length, 9/16 In Thread Length, Concretetight, Standard:UL 514B, Csa C22.2, Nema FB-1, Size:1.25IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce |
| Weight per unit  | 0.5000 (lbs/each)                                                                                                                                                                                                                                            |
| Product Category | Steel Insulated Straight Compr                                                                                                                                                                                                                               |

### Features

|                |                  |
|----------------|------------------|
| connection     | Male NPS Thread  |
| Connector Type | Compression      |
| insulation     | Insulated Throat |
| Material       | Steel            |

### Material, Color, and Finish

|        |                     |
|--------|---------------------|
| Color  | Metallic            |
| Finish | Zinc Electro Plated |

### Dimensions and Weight

|      |      |
|------|------|
| Size | 1.25 |
|------|------|

### Descriptions

|                        |                                                                                                                                                                                                                                                             |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 1-1/4 IN EMT COMP CONN IN                                                                                                                                                                                                                                   |
| extra long description | EGS 7125ST 1-1/4 IN EMT COMP CONN I                                                                                                                                                                                                                         |
| Long Description       | Features:1 13/16IN Dia X 2IN Length, 9/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:1.25IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE |
| Product Type           | 1-1/4 In Emt Comp Conn Insul Steel                                                                                                                                                                                                                          |
| Special Features       | 1 13/16 IN Dia X 2 IN Length, 9/16 IN Thread Length, Concretetight                                                                                                                                                                                          |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | APPOZGCOMM     |
| GTIN                      | 00687855873340 |
| Manufacturers Part Number | 7125ST         |
| UPC                       | 687855873340   |

### Taxonomies, Classifications, and Categories

|      |                                            |
|------|--------------------------------------------|
| Type | EMT Conduit Straight Compression Connector |
|------|--------------------------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

|            |      |
|------------|------|
| Trade Size | 1.25 |
|------------|------|

## Packaging

|        |   |
|--------|---|
| Carton | 5 |
|--------|---|

|         |    |
|---------|----|
| Package | 25 |
|---------|----|

|                 |     |
|-----------------|-----|
| Weight Per each | 0.5 |
|-----------------|-----|

## Uses, Certifications, and Standards

|             |                                                           |
|-------------|-----------------------------------------------------------|
| Application | To ground and secure EMT Raceways to boxes and enclosures |
|-------------|-----------------------------------------------------------|

|             |      |
|-------------|------|
| nema rating | FB-1 |
|-------------|------|

|          |                                                             |
|----------|-------------------------------------------------------------|
| standard | UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: |
|----------|-------------------------------------------------------------|

|  |                                                            |
|--|------------------------------------------------------------|
|  | C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507; |
|--|------------------------------------------------------------|

|  |            |
|--|------------|
|  | NEMA: FB-1 |
|--|------------|

|                    |    |
|--------------------|----|
| Temperature Rating | 90 |
|--------------------|----|