



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## 71333C 36W/48W/60W 3K/4K/5K Barn Light With Short Cap

*Morris Products Inc.*



Catalog Number	71333C
Manufacturer	Morris Products Inc.
Description	Led Area Light Fixture, Powder Coated Gray Finish; UI (Canada and Us), DLC Approval; Bracket Mounting; Led Lamp Type; 50 Watt Lamp Wattage; Die-Cast Aluminum Housing Material; 120/208/240/277 Volt Ac Lamp/Ballast Voltage
Weight per unit	7.5 (lbs/each)
Product Category	Led Roadway Lighting

### Features

Control Type	Twist Lock Photocell
Lamp Type	LED
Lamp Wattage	50 Watt
Lamp/Ballast Voltage	120/208/240/277 Volt AC
Reflector/Lens Type	Anti-Glare Polycarbonate Frosted Lens

### Material, Color, and Finish

Finish	Powder Coated Gray
Housing Material	Die-Cast Aluminum



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	Hardware Material Stainless Steel; Enclosure Rating IP65; Current Rating 0.6 Amp; Overall Dimension 21-1/4 Inch Depth x 24 Inch Height; Intensity 5050 Lumen; Efficacy Rating 101 Lumen per Watt; Color Rendering Index 72; Color Temperature Rating 5000 Kelvi
Commodity Description	Led Roadway Lighting
Description	36W/48W/60W 3K/4K/5K BARN LIGHT WITH SHORT CAP
extra long description	POWDER COATED GRAY FINISH; UL (CANADA AND US), DLC APPROVAL; BRACKET MOUNTING; LED LAMP TYPE; 50 WATT LAMP WATTAGE; DIE-CAST ALUMINUM HOUSING MATERIAL; 120/208/240/277 VOLT AC LAMP/BALLAST VOLTAGE; TWIST LOCK PHOTOCELL CONTROL TYPE; ANTI-GLARE POLYCARBONATE FROSTED LENS REFRACTOR/LENS TYPE; HARDWARE MATERIAL STAINLESS STEEL; ENCLOSURE RATING IP65; CURRENT RATING 0.6 AMP; OVERALL DIMENSION 21-1/4 INCH DEPTH X 24 INCH HEIGHT; INTENSITY 5050 LUMEN; EFFICACY RATING 101 LUMEN PER WATT; COLOR RENDERING INDEX 72;
Long Description	LED AREA LIGHT FIXTURE, POWDER COATED GRAY FINISH; UL (CANADA AND US), DLC APPROVAL; BRACKET MOUNTING; LED LAMP TYPE; 50 WATT LAMP WATTAGE; DIE-CAST ALUMINUM HOUSING MATERIAL; 120/208/240/277 VOLT AC LAMP/BALLAST VOLTAGE
Product Type	Led Area Light Fixture

## Manufacturer Information

Brand	Morris Products Inc.
GTIN	00601986713337
Manufacturers Part Number	71333C
UPC	601986713337

## Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	--

## Packaging

Carton	1
Weight Per each	7.5

## Uses, Certifications, and Standards

Approval	UL (Canada and US), DLC
Mounting	BRACKET