



# Core & Coil (71A) MH ~LT~ 175W

## CORE & COIL HID 71A5390001D

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information		Input Frequency	
ANSI Code	M90-M140	Input Frequency	60 Hz
Lamp Type	100 MH	Input Current (Open Circuit)	2.5/1.5/1.3/1.12 A
Number of Lamps	1 piece/unit	Input Current (Starting)	1.24/0.54/0.45/0.4 A
Circuit Type	HX-HPF	Input Current (Short Circuit)	0.63-0.95/0.43-0.65/0.37-0.55/0.29-0.44 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	1.35-1.7 A
Base Model	71A5390	Constant Wattage Deviation	12%
Core Size	3 X 4 (2 LW)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI533-H4	Open Circuit Voltage	260 V
Ignitor Temperature Rating	105°C	Input Current (Nom)	1.15/0.66/0.58/0.5 A A
Capacitor Value	12 MFD	Input Power (Nom)	129 W
Capacitor Catalog Number	7C120M30RA	Rated Lamp Power	100 W
Capacitor Requirements	280V	<b>Wiring</b>	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.65 in	Wire Length by Color	12"
Capacitor Height	2.75 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
<b>Operating and Electrical</b>		Max Ballast-Lamp Distance Remote Wiring	20'
Input Voltage	120/208/240/277 V	Recommended Fuse Value	10/5/5/4 A

## Core & Coil (71A) MH ~LT~ 175W

### Approval and Application

Open Circuit Voltage Test (Volts)	240-300 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	B/B/A/A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029B

### Product Data

Order product name	CORE & COIL HID 71A5390001D
EAN/UPC - Product	781087017838
Order code	913700533009
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700533009
Net Weight (Piece)	2.541 kg

### Dimensional drawing



MH BAL 100W 90/140 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5390001D	3.07 in	1.5 in	3.9 in	3.5 in	2.8 in	2.4 in

