



## Core & Coil (71A) MH 175W - 450W

# CORE & COIL HID MH BAL 320W M132/154 QUAD KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

#### **Product data**

General Information					
ANSI Code	M132-M154				
Lamp Type	320W MH				
Number of Lamps	1 piece/unit				
Circuit Type	SUPER-CWA				
Ballast Type	Magnetic HID				
Base Model	71A5892A				
Core Size	4 1/4 x 4 3/4 (2 coil)				
Suitable For Outdoor Use	Yes				
Ignitor Catalog Number	LI533-H4				
Ignitor Temperature Rating	105°C				
Capacitor Value	21 MFD				
Capacitor Catalog Number	7C210P34R				
Capacitor Requirements	345V				
Capacitor Temperature Rating	105°C				
Capacitor Diameter/Oval Dimensions	1.75 in				
Capacitor Height	4.8 in				
Automatic Restart	No				

Operating and Electrical						
Input Voltage	120/208/240/277 V					
Input Frequency	60 Hz					
Input Current (Open Circuit)	2.3/1.35/1.15/1 A					
Input Current (Starting)	1.8/1.05/0.9/0.8 A					
Input Current (Short Circuit)	1.65-2.5/1-1.5/0.8-1.25/0.7-1.1 A					
Secondary Short Circuit Current	2.9-3.6 A					
Constant Wattage Deviation	10%					
Ballast Factor (Nom)	1					
Power Factor (Nom)	0.90					
Open Circuit Voltage	270 V					
Input Current (Nom)	3.25/1.9/1.65/1.4 A A					
Input Power (Nom)	368 W					
Rated Lamp Power	320 W					
Wiring						
Wire Striplength	0.5 mm					
Wire Length by Color	12"					
Wire Type	Stranded					
Remote Wiring Configuration Allowed	Yes					


Datasheet, 2019, March 22 data subject to change

### Core & Coil (71A) MH 175W - 450W

Max Ballast-Lamp Distance Remote	2'				
Wiring					
Recommended Fuse Value	8/6/5/3 A				
Approval and Application					
Open Circuit Voltage Test (Volts)	250-300 V				
Approval Marks	ULR CSA certificate RoHS Compliant				
Temperature Marking	B/B/B/B				
UL Recognized	Yes				
Hipot Test (1 Minute)	2000 V				
Hipot Test (2 Seconds)	2500 V				
UL Insulation Class	H(180°C)				
UL Temperature Code	1029B				

Product Data			
Order product name	CORE & COIL HID MH BAL 320W M132/154		
	QUAD KIT		
EAN/UPC - Product	781087096178		
Order code	913700535309		
Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	1		
Material Nr. (12NC)	913700535309		
Net Weight (Piece)	5.149 kg		

### Dimensional drawing



MH BAL 320W M132/154 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 320W	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
M132/154 QUAD KIT						



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.