



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7474ASP 3/4" Insulated Duplex E-Z Lock Snap-In MC Connector

Bridgeport Fittings

| | |
|------------------|---|
| Catalog Number | 7474ASP |
| Manufacturer | Bridgeport Fittings |
| Description | 3/4" Insulated Duplex E-Z Lock Snap-In MC Connector |
| Weight per unit | 0.3700 (lbs/each) |
| Product Category | Boxes & Covers |

Features

| | |
|------------|---------------|
| insulation | Yes |
| Material | Zinc Die Cast |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Descriptions

| | |
|------------------------|---|
| Description | 3/4" INSULATED DUPLEX E-Z LOCK SNAP-IN MC CONNECTO |
| extra long description | BPT 7474ASP 3/4" INSUL DBL BARREL D |
| Long Description | 3/4" Insulated Duplex E-Z LOCK Snap-In MC Connector |
| Product Type | 3/4" Insul DBL Barrel Duplex C |
| Special Features | Listed for use with AC / AC90 / ACG90 / MC / MCI-A / HCFMCI-A / MC-PCS Cable*. cETLus Listed. |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747086938 |
| Manufacturers Part Number | 7474ASP |
| UPC | 781747086938 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | FORM 7, 8, CONDULETS, COVERS, & GASKETS |
| Type | Insulated Duplex E-Z LOCK® Snap-In MC Connector |

Packaging

| | |
|-----------------|------|
| Carton | 20 |
| Package | 100 |
| Weight Per each | 0.37 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Bridgeport's ASP line of E-Z LOCK® Duplex Snap-in Connectors offers superior installation speed with no tools required. To install, push the cables into the rear of the fitting, insert the fitting into the KO at an angle, and rock up to snap the front end in place. |
| standard | UL 514B |