# Eaton 7503BK-BOX

# Catalog Number: 7503BK-BOX

Eaton standard grade decorator switch, Box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Black, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 752452



## General specifications

UPC

032664752452

**Product Height** 

**Product Weight** 

Certifications cULus Listed

4.19 in

0.15 lb

 Product Name
 C

 Eaton standard grade decorator switch
 7

Catalog Number 7503BK-BOX Product Length/Depth

Product Width

0.97 in

1.44 in

Compliances NAFTA RoHS Compliant

Powering Business Worldwide

## Product specifications

## Special features

Box

## Switch type

Three-way

## Phase

Single-phase

## Load type

LED

- Motor Control
- Fan
- HAL
- FLR
- ELV
- INC
- CFL
- MLV

## Closure type

Maintained

## Color

Black

## Wiring method

Back and push

#### Material

Thermoplastic

## Mounting method

Flush

## Allowable wire size

#14-12 AWG

## Amperage Rating

15A

## Number Of Poles

Three-way

## Type Switch decorator

Voltage rating 120/277 V

## Resources

#### Brochures

Decorator standard grade switches spec sheet

## Specifications and datasheets

Eaton Specification Sheet - 7503BK-BOX

## Actuator

Decorator



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia