



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7555SS Turnlok Conn 3W 15A/125V 10A/250V *Pass & Seymour/Legrand*

Catalog Number	7555SS
Manufacturer	Pass & Seymour/Legrand
Description	Turnlok Connector 3WIRE 15AMP 125VOLT 10AMP 250V
Weight per unit	0.1710 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	15/10
Material	Nylon
Number of Wires	3
Poles	Consult the Factory
Voltage Rating	125/250
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	Consult the Factory

### Material, Color, and Finish

Color	Yellow
-------	--------

### Dimensions and Weight

Size	2.624 L x 1.531 H
------	-------------------

### Descriptions

Description	TURNLOK CONN 3W 15A/125V 10A/250V
extra long description	P&S 7555SS TURNLOK CONN 3W 15A/125V
Long Description	Turnlok Connector 3wire 15amp 125volt 10amp 250v
Product Type	Turnlok Conn 3W 15A/125V 10A/250V
Special Features	Industrial-strength plug blades and connector contacts resist heat rise, provide excellent conductivity. Impact- and corrosion-resistant durable nylon shell material. Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. Rounded back contour reduces snags and hang-ups on the job site. Visible stamped device rating.

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007755510
Manufacturers Part Number	7555SS
UPC	785007755510

### Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlok® Connector, Non-NEMA



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.171

## Uses, Certifications, and Standards

Application	Industrial
environmental conditions	Consult the Factory
Mounting	Cord
nema rating	Non-NEMA
standard	Non-NEMA