
NON-NEMA 3 WIRE FLANGED OUTLET, GRAY

7557SS | [Pass & Seymour](#)



FEATURES & BENEFITS

Flanged Outlet 15amp 125volt 10amp 250volt Turnlok

- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Type: Flanged Outlet
Number Of Wires: 3
Special Features: Non-NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 39121403

DIMENSIONS

Depth (US): 2.57"
Diameter (US): 2.56"

TECHNICAL INFORMATION

Amps: 15A
Volts: 250V
Volts (AC): 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant



