



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7802MD 30A 2P SNGL PH Ac Motor Disconnet

Pass & Seymour/Legrand

Catalog Number	7802MD
Manufacturer	Pass & Seymour/Legrand
Description	Motor Disconneter, 2 Poles, 30 A, 600 V Ac, 1.753 (L) X 1.825 (W) X 2.375 (H) In, Box Mount, -40 °C Operating Temperature, +75 °C Operating Temperature, Toggle Actuator, 0.31 LB
Weight per unit	0.3100 (lbs/each)
Product Category	Misc Wiring Devices

Features

actuator	Toggle
amperage rating	30
connection	Side & Back Wired
load	30A
operating cycles	50,000 cycles minimum, resistive, inductive, tungsten filament lamp load (Fed Spec)
Poles	2

Dimensions and Weight

Size	1.753" Depth x 1.825" Width x 2.375" Height
------	---

Descriptions

Description	30A 2P SNGL PH AC MOTOR DISCONNET
extra long description	P&S 7802MD 30A 2P SNGL PH AC MOTOR

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267655
Manufacturers Part Number	7802MD
UPC	785007267655

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Manual Controller

Packaging

Carton	1
Package	10
Weight Per each	0.31



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

environmental conditions	UL94 V2
Frequency Rating	60Hz
Mounting	BOX
Operating Temperature	Maximum continuous +75°C, minimum -40°C
standard	CSA Listed, UL Listed