



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7803MD 30A 3P 3 PH Ac Motor

Pass & Seymour/Legrand

Catalog Number	7803MD
Manufacturer	Pass & Seymour/Legrand
Description	Manual Control Switch, 3 Poles, 30 A, 600 V Ac, 1.7538 (L) X 1.825 (W) X 2.375 (H) In, Box Mount, -40 °C Operating Temperature, +75 °C Operating Temperature, Toggle Actuator, 0.335 LB
Weight per unit	0.3350 (lbs/each)
Product Category	Misc Wiring Devices

Features

actuator	Toggle
amperage rating	30
connection	Side & Back Wired
load	30A
Number of Phases	3.0
operating cycles	50000
Poles	3 Pole
Voltage	600.0 V
Wire Size	#14 - #10 Awg

Dimensions and Weight

Size	1.7538" Depth x 1.825" Width x 2.375" Height
------	--

Descriptions

Description	30A 3P 3 PH AC MOTOR
extra long description	P&S 7803MD 30A 3P 3 PH AC MOTOR
Special Features	Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267686
Manufacturers Part Number	7803MD
UPC	785007267686

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
Type	Manual Controller

Trade Size

Amperage	30.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.335

Uses, Certifications, and Standards

environmental conditions	UL94 V2
Frequency Rating	60Hz
Mounting	BOX
Operating Temperature	Maximum continuous +75°C, minimum -40°C
standard	CULUS, CSA Listed, UL Listed