
82548

F54T5 841/HO/ALTO (PK X 40)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Average Life Hours: 24000

Base: Miniature Bi-Pin (G5)

Bulb: T5

Coating: Copolymer

Color: 841

Color Temperature: 4100K

CRI: 85

Diameter: 0.63 IN

Initial Lumens: 5000

Lamp Type: Fluorescent

Length: 46.00 IN

Mean Design Lumens: 4450

Package (LxWxH): 46.75 IN x 6.75 IN x 4.25 IN

Package Weight: 12.95 L

Pack By: 40

Shape: T

Special Features: Shatter-Resistant

Type: Straight Linear Fluorescent Lamp

UPC: 726585825486

Voltage: 120 V

Wattage: 54.0 W

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone