



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8300IV Hubbell-Pro HG DPLX 20A/125V Iv *Hubbell Wiring Devices*

Catalog Number	8300IV
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Duplex Receptacle, Hospital Grade, Hubbell-Pro, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory.
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
pallet quantity	3600
Phase	1
Poles	2-Pole
Voltage Rating	125 VAC
Wattage	2,500
Wire Size	#12 to #10

Material, Color, and Finish

Color	Ivory
-------	-------

Dimensions and Weight

Size	3.28 in x 1.57 in x 1.15 in
------	-----------------------------

Descriptions

Description	HUBBELL-PRO HG DPLX 20A/125V IV
extra long description	HWDK 8300IV HUBBELL-PRO HG DPLX 20A
Long Description	Straight Blade Devices, Duplex Receptacle, Hospital Grade, Hubbell-Pro, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory.
Product Type	Hubbell-Pro HG DPLX 20A/125V Iv
Special Features	Self Grounding

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585197340
Manufacturers Part Number	8300IV
series	Hubbell-PRO
UPC	783585197340



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	RECEPTACLE

Packaging

Carton	1
Package	10
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Hubbell-Pro Heavy Duty Hospital Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA, C22.2, No. 42 File 285;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186