




Atlanta, Georgia

Phone 800-521-7326

Fax 770-745-1333

**Hex Machine Screw Nut
Zinc - 18-8 Stainless - 316 Stainless**



Peco Catalog#	Basic Tread Diameter	F			G		G1		H		
		Width Across Flats			Width Across Corners				Thickness		
		Basic	Min	Max	Square		Hex				
					Min	Max	Min	Max	Min	Max	
See Section Three of Our Catalog	0	0.0600	5/32	0.150	0.156	0.206	0.221	0.171	0.180	0.043	0.050
	1	0.0730	5/32	0.150	0.156	0.206	0.221	0.171	0.180	0.043	0.050
	2	0.0860	3/16	0.180	0.188	0.247	0.265	0.205	0.217	0.057	0.066
	3	0.0990	3/16	0.180	0.188	0.247	0.265	0.205	0.217	0.057	0.066
	4	0.1120	1/4	0.241	0.250	0.331	0.354	0.275	0.289	0.087	0.098
	5	0.1250	5/16	0.302	0.312	0.415	0.442	0.344	0.361	0.102	0.114
	6	0.1380	5/16	0.302	0.312	0.415	0.442	0.344	0.361	0.102	0.114
	8	0.1640	11/32	0.332	0.344	0.456	0.486	0.378	0.397	0.117	0.130
	10	0.1900	3/8	0.362	0.375	0.497	0.530	0.413	0.413	0.117	0.130
	12	0.2160	7/16	0.423	0.438	0.581	0.619	0.482	0.482	0.148	0.161
1/4	0.2500	7/16	0.423	0.438	0.581	0.619	0.482	0.482	0.178	0.193	

ANSI/ASME B18.6.3

Material	Steel : Any low carbon steel Stainless: 18-8 or 316 stainless steel
----------	--

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.