

Eaton 83-BOX

Catalog Number: 83-BOX

Eaton Arrow Hart extra heavy-duty angled plug , #12-10 AWG, 30A, Commercial, 125V, Back wire, Black, Brass, Urea, TT-30P, Two-pole, three-wire, grounding, Screw, 0.64", Thermoplastic, ED Box



General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty angled plug	83-BOX
	UPC
	032664752216
Product Length/Depth	Product Height
3.88 in	2.25 in
Product Width	Product Weight
2.94 in	0.268 lb
Warranty	Certifications
Refer to warranty document.	UL
	NOM
	Federal Specification Classification 6221 02

Product specifications

Special features

Travel trailer

Device type

Plug

Color

Black

Face/body material

Urea

Wiring method

Back wire

Features

Travel trailer

Material

Thermoplastic

Allowable wire size

#12-10 AWG

Amperage Rating

30A

Number Of Poles

Two-pole

Contact material

Brass

Type

Angled plug

Device grade

Extra heavy-duty industrial specification grade

NEMA configuration

TT-30P

Style type

Power, Angled body

Design type

Straight blade

Connection type

Screw

Resources

Brochures

Flush mount receptacles sell sheet

Catalogs

Residential Buyers Guide B-44

Specifications and datasheets

Eaton Specification Sheet - 83-BOX

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Cord range

0.64"

Voltage rating

125V

Application

Commercial

Torque rating

20-24 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)