

Eaton 8460N

Catalog Number: 8460N

Eaton power device receptacle, #14 to 10 AWG, 60A, Flush, 250V, Back and side, Black, NEMA 15-60R, Three-pole, Four-wire, Three-pole, four-wire, grounding, Screw, Glass-filled nylon, Three-phase, Power



General specifications

Product Name	Catalog Number
Eaton power device receptacle	8460N
UPC	Product Length/Depth
040893018690	3.25 in
Product Height	Product Width
2.38 in	2.94 in
Product Weight	Compliances
0.5 lb	RoHS Compliant

Certifications

cULus Listed
CSA Certified
Federal Specification Classification 6233
01

Product specifications

Phase

Three-phase

Color

Black

Wiring method

Back and side

Material

Glass filled nylon

Mounting method

Flush

Allowable wire size

#14-10 AWG

Amperage Rating

60A

Number Of Poles

Three-pole

NEMA configuration

15-60R

Design type

Receptacle

Connection type

Screw

Style

Power

Number of wires

4

Receptacle type

Three-pole, four-wire, grounding

Voltage rating

250 V

Torque rating

25 lbf-inch

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section A](#)

Specifications and datasheets

[Eaton Specification Sheet - 8460N](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)