



UL FILE No.:
 CONTROL No.:
 CSA No.:

856	2"	4.875	.750	2.030	6.050	2.890	1.400	2.400
855	1 1/2"	4.875	.750	1.585	6.050	2.385	1.400	2.400
854	1 1/4"	3.160	.625	1.300	3.080	2.135	1.625	1.940
853	1"	2.560	.625	1.000	2.510	1.680	1.330	1.570
852	3/4"	2.025	.475	.821	2.380	1.390	.770	1.205
851	1/2"	1.835	.415	.620	2.140	1.120	.635	1.085
850	3/8"	1.325	.360	.620	1.800	1.120	.440	.750
PART No.	TRADE SIZE	"A"	"B"	"C"	"D"	"E"	MIN	MAX