



CAT6 RJ-45 8P8C Standard Modular Plug

Modular plug designed for termination to CAT6 twisted pair cables. Plugs are 8 position – 8 contacts for use with Ethernet and related data applications. 3 piece design helps ensure twisted cable is assembled to CAT6 standards.

- 50µ gold plated contacts to minimize wear on individual contacts
- 3 prong contacts for secure connection to each wire
- 3 piece design with sled, liner and main connector body
- Primary and strain reliefs secures cable jacket in place
- Non-keyed (standard) connectors for use with standard crimpers
- Designed for 250MHz application compatibility (CAT6)
- Non-feed-thru design with closed end face.
- Fits cables with .290" jacket diameter
- Fits cables with 24 or 23 AWG solid/stranded conductors
- Recommended IDEAL cable jacket prep tool: 45-605
- Recommended crimp tools: 30-696, 30-496, 30-495, 33-396
- Compatible with non-IDEAL tools

Part No.	Qty
85-366	25/Card



Also available:



CAT6 Feed-Thru



30-496



30-696