

Eaton 8824 GGV NK

Catalog Number: 8824 GGV NK

Eaton B-Line series wiring trough, 8" height, 24" length, 8" width, GGV NK wireway, Thru holes, No knockouts, Screw cover, NEMA 1, Galvanized steel, Plated screws, Gray, 14 gauge

General specifications



Product Name

Eaton B-Line series wiring trough

Catalog Number

8824 GGV NK

UPC

782051009682

Product Length/Depth

24 in

Product Height

8 in

Product Width

8 in

Product Weight

13.54 lb

Certifications

CSA Certified

UL Listed



Powering Business Worldwide

Material/finish

Material thickness

14 gauge

Finish color

Gray

Model

Closure type

Plated screws

Mounting method

Thru holes

Special features

Cover is secured with plated screws

Type

GGV NK wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 8824 GGV NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)